



Click [here](#) for the 3D model.

**General Information**

|              |                                |
|--------------|--------------------------------|
| Series       | A759                           |
| Dielectric   | Polymer Aluminum               |
| Description  | Single Ended, Polymer Aluminum |
| RoHS         | Yes                            |
| Lead         | Cut                            |
| Halogen Free | Yes                            |

| Dimensions |                 |
|------------|-----------------|
| D          | 10mm +/-0.5mm   |
| L          | 12mm +/-1mm     |
| S          | 5mm +/-0.5mm    |
| F          | 0.6mm +/-0.05mm |

  

| Packaging Specifications |           |
|--------------------------|-----------|
| Packaging                | Bulk, Bag |
| Packaging Quantity       | 250       |

| Specifications     |  |
|--------------------|--|
| Capacitance        | 100 uF   |
| Tolerance          | 20%  |
| Voltage DC         | 50 VDC, 57.5 VDC (Surge)   |
| Temperature Range  | -55/+125°C   |
| Rated Temperature  | 125°C  |
| Life               | 2000 Hrs (+/-20% Initial Capacitance, 1.5x DF MAX, Leakage Within Limit) |
| Dissipation Factor | 12% 120Hz 20C  |
| ESR                | 31 mOhms (100kHz 20C)  |
| Ripple Current     | 2830 mAmps (100kHz 105C), 1650 mAmps (100kHz 125C)                       |
| Leakage Current    | 750 uA (2min 20°C)   |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.