


A927KF113Q063W

A927, Aluminum, Aluminum Electrolytic, 11,000 uF, -10/+30%, 63 VDC, -40/+150°C



General Information

Series	A927
Dielectric	Aluminum Electrolytic
Style	Module
Description	Aluminum Electrolytic Capacitor Module
RoHS	Yes
Qualifications	AEC-Q200
Halogen Free	Yes
Typical Component Weight	144 g
Shelf Life	520 Weeks

Dimensions

X	135mm +/-1mm
Y	60mm +/-1mm
Z	31mm +/-1mm

Packaging Specifications

Packaging	Bulk
Packaging Quantity	1

Specifications

Capacitance	11,000 uF
Tolerance	-10/+30%
Voltage DC	63 VDC (125C), 54 VDC (150C)
Temperature Range	-40/+150°C
Rated Temperature	125°C
Life	8400 Hrs, 2000 Hrs (Derated Voltage At 150C)
ESR	9 mOhms (100Hz 20C), 4.5 mOhms (100kHz 20C), 3 mOhms (100kHz 150C)
Ripple Current	93.6 Amps (5kHz 125C), 59.2 Amps (5kHz 140C), 26.4 Amps (5kHz 150C)
Leakage Current	2083 uA (5min 20°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.