

ALC40A391BC200

ALC40, Aluminum, Aluminum Electrolytic, 390 uF, 20%, 200 VDC, -40/+105°C, 10 mm



Click [here](#) for the 3D model.

Dimensions	
D	25mm +1mm
L	35mm +/-2mm
S	10mm +/-0.1mm
LL	6.3mm +/-1mm
F	2mm +/-0.1mm

Packaging Specifications	
Packaging	Tray

General Information	
Series	ALC40
Dielectric	Aluminum Electrolytic
Description	Snap-In, Aluminum Electrolytic
RoHS	Yes
Lead	2 Pin
Typical Component Weight	29.3 g
Shelf Life	156 Weeks

Specifications	
Capacitance	390 uF
Tolerance	20%
Voltage DC	200 VDC, 230 VDC (Surge)
Temperature Range	-40/+105°C
Rated Temperature	105°C
Life	6000 Hrs (Rated Voltage And Ripple Current At 105C), 10000 Hrs (Rated Voltage at 105C)
ESR	386 mOhms (100Hz 20C), 271 mOhms (10kHz 20C)
Ripple Current	1.24 Amps (100Hz 105C), 1.86 Amps (10kHz 105C)
Leakage Current	234 uA (5min 20°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.