



Click [here](#) for the 3D model.

**Dimensions**

D	25mm +1mm
L	40mm +/-2mm
S	10mm +/-0.1mm
LL	4mm +/-1mm
F	2mm +/-0.1mm

**Packaging Specifications**

Sleeving	Yes
Packaging	Bulk, Bag

**General Information**

Series	ALC70
Dielectric	Aluminum Electrolytic
Description	Snap-In, Aluminum Electrolytic
RoHS	Yes
Lead	2 Pin Short
Halogen Free	Yes
Typical Component Weight	35 g
Notes	Dimensions D And L Include Sleeving.
Shelf Life	156 Weeks

**Specifications**

Capacitance	9,100 uF
Tolerance	20%
Voltage DC	40 VDC, 46 VDC (Surge)
Temperature Range	-40/+85°C
Rated Temperature	85°C
Life	10000 Hrs (Rated Voltage And Ripple Current At 85C), 16000 Hrs (Rated Voltage at 85C)
ESR	83.38 mOhms (100Hz 20C), 69.23 mOhms (10kHz 20C)
Ripple Current	4.21 Amps (100Hz 85C), 5.303 Amps (10kHz 85C)
Leakage Current	2184 uA (5min 20°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.