



Please see datasheet for details on PCB hole size and tolerance

Click [here](#) for the 3D model.

#### General Information

Series	ALF20
Dielectric	Aluminum Electrolytic
Style	Press-Fit
Description	Aluminum Electrolytic
RoHS	Yes
Lead	4 Pin Press-Fit
Typical Component Weight	49 g
Notes	Dimensions Include Slewing.
Shelf Life	156 Weeks

#### Dimensions

D	40mm +1mm
L	30mm +/-2mm
S	22.5mm +/-0.1mm
LL	5.5mm +/-1mm
F	1.486mm +/-0.076mm

#### Packaging Specifications

Packaging	Bulk
Packaging Quantity	72

#### Specifications

Capacitance	270 uF
Tolerance	20%
Voltage DC	400 VDC, 440 VDC (Surge)
Temperature Range	-40/+85°C
Rated Temperature	85°C
Life	18000 Hrs (Rated Voltage And Ripple Current At 85C), 29000 Hrs (Rated Voltage At 85C)
ESR	441 mOhms (100Hz 20C), 284 mOhms (10kHz 20C)
Ripple Current	1.85 Amps (100Hz 85C), 3.67 Amps (10kHz 85C)
Leakage Current	648 uA (5min 20°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.