

## ALF80G112EH350

ALF80, Aluminum, Aluminum Electrolytic, 1,100 uF, 20%, 350 VDC, -40/+105°C, 25 mm



Click [here](#) for the 3D model.

### General Information

Series	ALF80
Dielectric	Aluminum Electrolytic
Style	Press-Fit
Description	Aluminum Electrolytic
RoHS	Yes
Lead	5 Pin Press-Fit
Typical Component Weight	125 g
Notes	Dimensions D And L Include Sleaving.
Shelf Life	156 Weeks

Dimensions	
D	40mm +1mm
L	60mm +/-2mm
S	25mm +/-0.1mm
LL	5.5mm +/-1mm
F	1.486mm +/-0.076mm

  

Packaging Specifications	
Sleaving	Yes
Packaging	Bulk

Specifications	
Capacitance	1,100 uF
Tolerance	20%
Voltage DC	350 VDC, 385 VDC (Surge)
Temperature Range	-40/+105°C
Rated Temperature	105°C
Life	9000 Hrs (Rated Voltage And Ripple Current At 105C), 14000 Hrs (Rated Voltage at 105C)
ESR	131.8 mOhms (100Hz 20C), 71.35 mOhms (10kHz 20C)
Ripple Current	4.262 Amps (100Hz 105C), 9.519 Amps (10kHz 105C)
Leakage Current	1155 uA (5min 20°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.