

## ALS70G562NP500

ALS70, Aluminum, Aluminum Electrolytic, 5,600 uF, 20%, 500 VDC, -40/+85°C, 31.8 mm



Click [here](#) for the 3D model.

### General Information

|                          |   |
|--------------------------|---|
| Series                   | ALS70   |
| Dielectric               | Aluminum Electrolytic   |
| Description              | Screw Terminal, Aluminum Electrolytic   |
| RoHS                     | Yes   |
| Lead                     | Screw Terminals M6  |
| Mounting                 | Through-Hole  |
| Halogen Free             | Yes   |
| Typical Component Weight | 960 g   |
| Notes                    | Dimensions D And L Include Sleeving. MS (MxH) = M12x16. Mounting Clamp (Sold Separately): V11 |
| Shelf Life               | 156 Weeks   |

### Dimensions

|    |                      |
|----|----------------------|
| D  | 77mm +/-1mm          |
| L  | 146mm +/-2mm         |
| T  | 6.4mm +/-0.5mm       |
| S  | 31.8mm +/-0.5mm      |
| DT | 17mm +/-0.5mm        |
| LT | Available On Request |
| TD | 11.8mm MIN           |
| V  | 19mm NOM             |

### Packaging Specifications

|           |      |
|-----------|------|
| Sleeving  | Yes  |
| Packaging | Tray |

### Specifications

|                   |   |
|-------------------|---|
| Capacitance       | 5,600 uF  |
| Tolerance         | 20%   |
| Voltage DC        | 500 VDC, 550 VDC (Surge)  |
| Temperature Range | -40/+85°C   |
| Rated Temperature | 85°C  |
| Life              | 20000 Hrs (Rated Voltage And Ripple Current At 85C), 40000 Hrs (Rated Voltage at 85C) |
| ESR               | 50 mOhms (100Hz 20C), 38 mOhms (10kHz 20C)  |
| Ripple Current    | 16.6 Amps (100Hz 85C), 24 Amps (10kHz 85C)  |
| Leakage Current   | 6000 uA   |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.