
# ALS70H272LM550

ALS70, Aluminum Electrolytic, 2,700 uF, 20%, 550 VDC, -40/+85°C, 28.5 mm




Click here for the 3D model.

| General Information | |
|---|---|
| Series | ALS70 |
| Dielectric | Aluminum Electrolytic |
| Description | Screw Terminal, Aluminum Electrolytic |
| RoHS | Yes |
| Mounting | Through-Hole |
| Halogen Free | Yes |
| Typical Component Weight | 600 g |
| Notes | Dimensions D And L Include Sleeving. MS (MxH) = M12x16. Mounting Clamp (Sold Separately): V8 |
| Shelf Life | 156 Weeks |

| Dimensions | |
|---|---|
| D | 63.5mm +/-1mm |
| L | 131mm +/-2mm |
| T | 7.1mm +/-0.5mm |
| S | 28.5mm +/-0.5mm |
| DT | 8mm +/-0.5mm |
| LT | Available On Request |
| TD | 10mm MIN |
| V | 15.8mm NOM |

| Packaging Specifications | |
|---|---|
| Sleeving | Yes |
| Packaging | Tray |

| Specifications | |
|---|---|
| Capacitance | 2,700 uF |
| Tolerance | 20% |
| Voltage DC | 550 VDC, 605 VDC (Surge) |
| Temperature Range | -40/+85°C |
| Rated Temperature | 85°C |
| Life | 19000 Hrs (Rated Voltage And Ripple Current At 85C), 38000 Hrs (Rated Voltage at 85C) |
| ESR | 161 mOhms (100Hz 20C), 140 mOhms (10kHz 20C) |
| Ripple Current | 11.4 Amps (100Hz 85C), 17.5 Amps (10kHz 85C) |
| Leakage Current | 6000 uA |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.



© 2006 - 2026 YAGEO