


[Click here for the 3D model.](#)

General Information

Series	ALS71
Dielectric	Aluminum Electrolytic
Description	Screw Terminal, Aluminum Electrolytic
RoHS	Yes
Lead	Oval Threaded Inserts M5
Mounting	Through-Hole
Optional Mounting	Stud
AEC-Q200	No
Halogen Free	Yes
Typical Component Weight	220 g
Notes	Dimensions D And L Include Sleaving. MS (MxH) = M12x16. Mounting Clamp (Sold Separately): V4/2737
Shelf Life	156 Weeks

Dimensions

D	51mm +/-1mm	Capacitance	2,400 uF
L	82mm +/-2mm	Tolerance	20%
T	5.5mm +/-0.5mm	Voltage DC	350 VDC, 385 VDC (Surge)
S	22.2mm +/-0.5mm	Temperature Range	-40/+85°C
DT	13mm +/-0.5mm	Rated Temperature	85°C
LT	86.5mm +/-1mm	Life	18000 Hrs (Rated Voltage And Ripple Current At 85C), 36000 Hrs (Rated Voltage at 85C)
TD	10mm MIN	ESR	80 mOhms (100Hz 20C), 49 mOhms (10kHz 20C)
V	13.7mm NOM	Ripple Current	8.1 Amps (100Hz 85C), 13.6 Amps (10kHz 85C)
Z	10mm NOM	Leakage Current	5040 uA

Packaging Specifications

Sleeving	Yes
Packaging	Tray

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.