

## ALS80H681DE450

ALS80, Aluminum, Aluminum Electrolytic, 680 uF, 20%, 450 VDC, -40/+105°C, 12.8 mm



Click [here](#) for the 3D model.

### General Information

|                          |   |
|--------------------------|---|
| Series                   | ALS80   |
| Dielectric               | Aluminum Electrolytic   |
| Description              | Screw Terminal, Aluminum Electrolytic   |
| RoHS                     | Yes   |
| Lead                     | Threaded Inserts - 10-32 UNF class 2B   |
| Mounting                 | Through-Hole  |
| Halogen Free             | Yes   |
| Typical Component Weight | 115 g   |
| Notes                    | Dimensions D And L Include Sleeving. MS (MxH) = M8x12. Mounting Clamp (Sold Separately): V3/H2/2736 |
| Shelf Life               | 156 Weeks   |

### Dimensions

|    |                      |
|----|----------------------|
| D  | 36mm +/-1mm          |
| L  | 82mm +/-2mm          |
| T  | 7.1mm +/-0.5mm       |
| S  | 12.8mm +/-0.5mm      |
| DT | 8mm +/-0.5mm         |
| LT | Available On Request |
| TD | 10mm MIN             |
| V  | 8mm NOM              |

### Packaging Specifications

|           |      |
|-----------|------|
| Sleeving  | Yes  |
| Packaging | Tray |

### Specifications

|                   |  |
|-------------------|--|
| Capacitance       | 680 uF   |
| Tolerance         | 20%  |
| Voltage DC        | 450 VDC, 495 VDC (Surge)   |
| Temperature Range | -40/+105°C   |
| Rated Temperature | 105°C  |
| Life              | 6000 Hrs (Rated Voltage And Ripple Current At 105C), 10000 Hrs (Rated Voltage at 105C) |
| ESR               | 228 mOhms (100Hz 20C), 140 mOhms (10kHz 20C)   |
| Ripple Current    | 3.5 Amps (100Hz 105C), 8.7 Amps (10 kHz 105C)  |
| Leakage Current   | 918 uA   |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.