



Click [here](#) for the 3D model.

**General Information**

|                          |                                       |
|--------------------------|---------------------------------------|
| Series                   | SMD Comm Y5V                          |
| Style                    | SMD Chip                              |
| Description              | SMD, MLCC, General Purpose, Class III |
| Features                 | Class III                             |
| RoHS                     | Yes                                   |
| Termination              | Tin                                   |
| Marking                  | No                                    |
| Typical Component Weight | 6.5 mg                                |
| Shelf Life               | 78 Weeks                              |
| MSL                      | 1                                     |

**Specifications**

|  |   |
|--|---|
| Capacitance  | 1uF   |
| Measurement Condition  | 1 kHz 1.0Vrms                                 |
| Tolerance  | -20/+80%                                      |
| Voltage DC   | 25 VDC  |
| Dielectric Withstanding Voltage                                    | 62.5 VDC                                      |
| Temperature Range  | -30/+85°C                                     |
| Temp. Coefficient  | Y5V   |
| Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC) | +22%/-82%, 1kHz 1.0Vrms                       |
| Dissipation Factor   | 10% 1 kHz 1.0Vrms                             |
| Aging Rate   | 7% Loss/Decade Hour: Referee Time is 48 Hours |
| Insulation Resistance  | 100 MOhms                                     |

**Dimensions**

|                      |                  |
|----------------------|------------------|
| L                    | 1.6mm +/-0.15mm  |
| W                    | 0.8mm +/-0.15mm  |
| T                    | 0.8mm +/-0.10mm  |
| S                    | 0.5mm MIN        |
| B                    | 0.35mm +/-0.15mm |
| Case Code (EIA / mm) | 0603 / 1608      |

**Packaging Specifications**

|                    |                        |
|--------------------|------------------------|
| Packaging          | T&R, 180mm, Paper Tape |
| Packaging Quantity | 4000                   |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.