



Click [here](#) for the 3D model.

#### General Information

|              |                                      |
|--------------|--------------------------------------|
| Series       | LDD Comm X7R                         |
| Style        | Radial                               |
| Features     | Commercial                           |
| RoHS         | With Exemptions                      |
| REACH        | SVHC (Pb - CAS 7439-92-1)            |
| SCIP Number  | ff8834ac-5013-4064-ad05-4cd1f8f13378 |
| Termination  | Tin                                  |
| Lead         | Wire Leads                           |
| Failure Rate | N/A                                  |

#### Dimensions

|    |                         |
|----|-------------------------|
| L  | 7.37mm +/-0.25mm        |
| H  | 7.37mm +/-0.25mm        |
| T  | 2.29mm +/-0.25mm        |
| S  | 5.08mm +/-0.38mm        |
| LL | 31.75mm MIN             |
| F  | 0.635mm +0.102/-0.051mm |

#### Packaging Specifications

|                    |                     |
|--------------------|---------------------|
| Packaging          | T&R, 305mm, Type II |
| Packaging Quantity | 1500                |

#### Specifications

|                                 |                |
|---------------------------------|----------------|
| Capacitance                     | 2,700 pF       |
| Tolerance                       | 10%            |
| Voltage DC                      | 200 VDC        |
| Dielectric Withstanding Voltage | 500 VDC        |
| Temperature Range               | -55/+125°C     |
| Temp. Coefficient               | X7R            |
| Dissipation Factor              | 2.5% 1 kHz 25C |
| Insulation Resistance           | 370 MOhms      |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.