



Click [here](#) for the 3D model.

**General Information**

|                |                            |
|----------------|----------------------------|
| Series         | AxiMax 400 Auto X8R HT150C |
| Description    | AxiMax, Automotive Grade   |
| Features       | Automotive Grade           |
| RoHS           | Yes                        |
| Termination    | Tin                        |
| Lead           | Wire Leads                 |
| Failure Rate   | N/A                        |
| Qualifications | AEC-Q200                   |
| Halogen Free   | Yes                        |

**Dimensions**

|    |                        |
|----|------------------------|
| D  | 2.41mm MAX             |
| L  | 4.32mm MAX             |
| LL | 25.4mm MIN             |
| F  | 0.51mm +0.025/-0.076mm |

**Packaging Specifications**

|                    |           |
|--------------------|-----------|
| Packaging          | Bulk, Bag |
| Packaging Quantity | 300       |

**Specifications**

|  |                     |
|--|---------------------|
| Capacitance  | 330 pF              |
| Measurement Condition  | 1 MHz 1.0Vrms       |
| Tolerance  | 5%                  |
| Voltage DC   | 100 VDC             |
| Dielectric Withstanding Voltage                                    | 250 VDC             |
| Temperature Range  | -55/+150°C          |
| Temp. Coefficient  | X8R                 |
| Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC) | 0.15, 1MHz 1.0Vrms  |
| Dissipation Factor   | 2.5% 1 MHz 1.0Vrms  |
| Aging Rate   | 0% Loss/Decade Hour |
| Insulation Resistance  | 100 GOhms           |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.