



Click [here](#) for the 3D model.

#### General Information

Series	C4AQ-M
Dielectric	Metallized Polypropylene
Style	Radial
RoHS	Yes
Lead	Wire Leads
Qualifications	AEC-Q200, IEC61071, EN61071, VDE0560
Typical Component Weight	17.9 g
Miscellaneous	Rth = 39 C/W.

Dimensions	
L	32mm +0.5/-0.7mm
H	15mm +0.2/-0.7mm
T	24mm +0.3/-0.7mm
S	27.5mm +/-0.4mm
LL	6mm +0/-2mm
F	0.8mm +/-0.05mm

Specifications	
Capacitance	2.1 uF
Tolerance	5%
Voltage DC	1100 VDC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Insulation Resistance	14.3 GOhms
Max dV/dt	80 V/us
ESR	17.5 mOhms (10kHz 70C)
Ripple Current	6.2 Amps Irms (10kHz 70C), 168 Amps Ipk
Inductance	13 nH

Packaging Specifications	
Packaging	Bulk, Box
Packaging Quantity	168

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.