
C9TS6MD5548AARX

C9T, Film, Metallized Polypropylene, AC Filter, 54.8 uF, -5/+10%, 440 VAC



General Information	
Series	C9T
Dielectric	Metallized Polypropylene
Style	Can
Features	Three Phase PFC
RoHS	Yes
Lead	Quick Connect
Qualifications	VDE
Typical Component Weight	953 g
Miscellaneous	Q = 10 kvar. Operating Freq. = 50 Hz.

Click here for the 3D model.

Dimensions	
D	85mm +/-0.5mm
L	160mm +/-2mm

Packaging Specifications	
Terminal Type	Bolt - M12x16
Packaging	Bulk, Bag
Packaging Quantity	9

Specifications	
Capacitance	54.8 uF
Tolerance	-5/+10%
Voltage AC	440 VAC
Temperature Range	-25/+55°C
Rated Temperature	55°C
Max dV/dt	30 V/us
Irms	17 A

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

© 2006 - 2026 YAGEO