
# CC0805GKNPOZBN102

Please contact sales for availability

CC HV, Ceramic, 1,000 pF, 2%, 630 VDC, C0G, 0805 / 2012




Click here for the 3D model.

| General Information | |
|---|---|
| Series | CC HV |
| Style | SMD Chip |
| RoHS | Yes |
| Termination | Tin |

| Dimensions | |
|---|---|
| L | 2mm +/-0.2mm |
| W | 1.25mm +/-0.2mm |
| T | 1.25mm +/-0.2mm |
| B | 0.5mm +/-0.25mm |
| Case Code (EIA / mm) | 0805 / 2012 |

| Packaging Specifications | |
|---|---|
| Packaging | T&R, 178mm, Plastic Tape |
| Packaging Quantity | 3000 |

| Specifications | |
|---|---|
| Capacitance | 1,000 pF |
| Tolerance | 2% |
| Voltage DC | 630 VDC |
| Temperature Range | -55/+125°C |
| Temp. Coefficient | C0G |
| Dissipation Factor | 0.1% |
| Insulation Resistance | 10 GOhms |
| Endurance (% Rated voltage) | 130% |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.



© 2006 - 2026 YAGEO