



Note: '()' correspond to the letters used in the product bulletin

Click [here](#) for the 3D model.

General Information

Series	F161
Dielectric	Metallized Polyester Stacked
Style	SMD Chip
Features	Automotive Grade
RoHS	Yes
Qualifications	AEC-Q200
Typical Component Weight	1.591 g
Shelf Life	104 Weeks
MSL	3

Dimensions	
L	10.2mm +/-0.2mm
W	9.1mm +/-0.2mm
T	5.5mm +/-0.2mm
F	0.5mm NOM
Case Code (EIA / mm)	4036 / 10091

Packaging Specifications	
Packaging	T&R
Packaging Quantity	800

Specifications	
Capacitance	1uF
Tolerance	10%
Voltage DC	50 VDC
Voltage AC	30 VAC
Temperature Range	-55/+125°C
Rated Temperature	85°C
Dissipation Factor	0.8% 1kHz, 1.5% 10kHz
Insulation Resistance	400 MOhms
Max dV/dt	12 V/us

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.