


MR-3

Aliases (USEZ3000000000)

KEMET, MR, Current, Round - Toroidal, Zero Phase Current, High Sensitivity, Compact



Click [here](#) for the 3D model.

General Information

Series	MR
Type	Current
Style	Round - Toroidal
Description	Zero-Phase Current Transformers
Features	High Sensitivity, Compact
Lead	Cables
RoHS	Yes
REACH	Yes
Notes	Measurement Conditions: f=60Hz, R=300 Ohms, I _o =22.5 mAmps

Dimensions

D	11mm MIN
H	10.5mm MAX
D2	28mm MAX
D3	30.5mm MAX
D4	6mm NOM
LL	67mm +/-3mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	300
Typical Component Weight	11.9 g

Specifications

Temperature Range	-20/+80°C
Voltage DC	8 mV MIN (Output)
Current	60 Amps
ESR	30 Ohms
Miscellaneous	Overinput characteristics (After DC5A input) = 10% MAX.

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.