

## PME271E622KR30

Aliases (P277EJ224K300A)

Obsolete

PME271E/P277, Film, Metallized Paper, Safety, 0.22 uF, 10%, 630 VDC, 300 VAC (X1), 110°C, 25.4 mm



Click [here](#) for the 3D model.

### General Information

Series	PME271E/P277
Dielectric	Metallized Paper
Style	Radial
Features	EMI Safety
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
Safety Class	X1
Qualifications	ENEC, UL, cUL
Construction	Molded
Typical Component Weight	9 g
Miscellaneous	SRF= 2.6 MHz.

### Dimensions

L	30.5mm MAX
H	19mm MAX
T	12.1mm MAX
S	25.4mm +/-0.4mm
LL	30mm +5mm
F	1mm +/-0.05mm

### Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	100

### Specifications

Capacitance	0.22 uF
Tolerance	10%
Voltage DC	630 VDC
Voltage AC	300 VAC (X1)
Temperature Range	-40/+110°C
Rated Temperature	110°C
Dissipation Factor	1.3% 1kHz
Insulation Resistance	12 GOhms
Max dV/dt	400 V/us

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.