



Note: '()' correspond to the letters used in the product bulletin
Click [here](#) for the 3D model.

General Information

Series	PZB300/P300
Dielectric	Metallized Paper
Style	Radial
Features	EMI Safety
RoHS	Yes
Termination	Tinned Wire
Lead	3 Leads
Safety Class	Delta EMI X2+Y2+Y2
Qualifications	ENEC, UL, cUL
Construction	Molded
Typical Component Weight	6.75 g
Miscellaneous	y2_cap_value= 0.0022 uF.

Dimensions

L	24mm MAX
H	16mm MAX
T	12.5mm MAX
S	20mm +/-0.5mm
S1	10mm NOM
LL	30mm +5mm
F	0.8mm +/-0.05mm

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	150

Specifications

Capacitance	0.15 uF
Tolerance	20%
Voltage AC	275 VAC
Temperature Range	-40/+100°C
Rated Temperature	100°C
Dissipation Factor	1.3% 1kHz
Insulation Resistance	12 GOhms
Max dV/dt	600 V/us