



Click [here](#) for the 3D model.

**General Information**

Series	PEH169
Dielectric	Aluminum Electrolytic
Description	Screw Terminal, Aluminum Electrolytic
RoHS	Yes
Lead	Oval Threaded Inserts M5
Mounting	Through-Hole
Optional Mounting	Stud
Halogen Free	Yes
Typical Component Weight	1,400 g
Notes	Dimensions D And L Include Slewing. M5. MS = M12x16.
Shelf Life	156 Weeks

**Dimensions**

D	91.6mm +/-1mm
L	145.5mm +/-1mm
T	3.7mm NOM
S	32mm +/-0.5mm
F	15mm +/-0.5mm
DT	15mm NOM
G	13mm NOM
LT	152.4mm +/-1mm
Z	13mm NOM

**Packaging Specifications**

Slewing	Yes
Packaging	Bulk, Bag
Packaging Quantity	6

**Specifications**

Capacitance	3,300 uF
Tolerance	20%
Voltage DC	450 VDC
Temperature Range	-40/+85°C
Rated Temperature	85°C
Life	38000 Hrs (Rated Voltage And Ripple Current At 85C), 78000 Hrs (Rated Voltage At 85C)
ESR	35 mOhms (100Hz 20C), 25 mOhms (100kHz 20C)
Ripple Current	12.6 Amps (100Hz 85C), 30.9 Amps (10kHz 50C), 28.3 Amps (10kHz 40C)
Leakage Current	8455 uA (5min 20°C)
Inductance	16 nH (ESL)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.