



Click [here](#) for the 3D model.

**General Information**

Series	PEH200
Dielectric	Aluminum Electrolytic
Description	Screw Terminal, Aluminum Electrolytic
RoHS	Yes
Lead	Screw Terminals M5
Mounting	Through-Hole
Optional Mounting	Stud
Halogen Free	Yes
Typical Component Weight	130 g
Notes	Dimensions D And L Include Slewing. MS = M8x12.
Shelf Life	156 Weeks

**Dimensions**

D	36.6mm +/-1mm
L	94.5mm +/-1mm
T	4.4mm NOM
S	13mm +/-0.5mm
DT	8mm NOM
LT	101.9mm +/-1mm

**Packaging Specifications**

Slewing	Yes
Packaging	Bulk, Bag
Packaging Quantity	42

**Specifications**

Capacitance	10,000 uF
Tolerance	20%
Voltage DC	63 VDC
Temperature Range	-40/+85°C
Rated Temperature	85°C
Life	10000 Hrs (Rated Voltage And Ripple Current At 85C)
ESR	15 mOhms (100Hz 20C), 10 mOhms (100kHz 20C)
Ripple Current	13.6 Amps (100Hz 85C), 36 Amps (10kHz 50C), 27 Amps (10kHz 40C)
Leakage Current	5890 uA (5min 20°C)
Inductance	12 nH (ESL)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.