



Click [here](#) for the 3D model.

**General Information**

Series	PHS225
Dielectric	Hybrid Polymer
Style	Horizontal SMD
Description	Horizontal Surface Mount Hybrid Polymer
RoHS	Yes
Lead	Radial SMD
Qualifications	AEC-Q200
Halogen Free	Yes
Typical Component Weight	15 g
Shelf Life	520 Weeks

**Specifications**

Capacitance	370 uF
Tolerance	-10/+30%
Voltage DC	63 VDC
Temperature Range	-40/+125°C
Rated Temperature	125°C
ESR	147 mOhms (100Hz 20C), 7.3 mOhms (100kHz 125C)
Ripple Current	38.3 Amps (100kHz 90C), 30 Amps (100kHz 105C), 17.2 Amps (100kHz 125C)
Leakage Current	116.5 uA (5min 20°C)

**Dimensions**

L	43mm +/-1mm
L1	49.2mm MIN
W	18mm +/-0.5mm
H	17.2mm +/-0.5mm
T	4mm +/-0.3mm

**Packaging Specifications**

Packaging	Tray
-----------	------

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.