



Click [here](#) for the 3D model.

General Information

| | |
|--------------------------|--------------------------|
| Series | R46 310 VAC 125C |
| Dielectric | Metallized Polypropylene |
| Style | Radial |
| Features | EMI Safety |
| RoHS | Yes |
| Termination | Tinned Wire |
| Lead | Wire Leads |
| Safety Class | X2 |
| Qualifications | ENEC, UL, cUL, CQC |
| Typical Component Weight | 1.215 g |

Dimensions

| | |
|----|--------------------|
| L | 18mm +0.3/-0.5mm |
| H | 17.5mm +0.1/-0.5mm |
| T | 6mm +0.2/-0.5mm |
| S | 15mm +/-0.4mm |
| LL | 30mm +5mm |
| F | 0.6mm +/-0.05mm |

Packaging Specifications

| | |
|--------------------|-----------|
| Packaging | Bulk, Bag |
| Packaging Quantity | 700 |

Specifications

| | |
|-----------------------|--------------|
| Capacitance | 0.15 uF |
| Tolerance | 20% |
| Voltage DC | 630 VDC |
| Voltage AC | 310 VAC (X2) |
| Temperature Range | -40/+125°C |
| Rated Temperature | 125°C |
| Dissipation Factor | 0.3% 1kHz |
| Insulation Resistance | 100 GOhms |
| Max dV/dt | 400 V/us |