

## R66DD3470DQ6AJ

Aliases (66DD3470DQ6AJ)

R66, Film, Metallized Polyester Stacked, Automotive Grade, 0.47 uF, 5%, 63 VDC, 85°C, 7.5 mm



Click [here](#) for the 3D model.

### General Information

|                          |  |
|--------------------------|--|
| Series                   | R66  |
| Dielectric               | Metallized Polyester Stacked                     |
| Style                    | Radial   |
| Features                 | Automotive Grade, DC Multipurpose Applications   |
| RoHS                     | Yes  |
| Termination              | Tinned Wire                                      |
| Lead                     | Wire Leads                                       |
| Qualifications           | AEC-Q200   |
| Typical Component Weight | 0.41 g   |
| Miscellaneous            | Above 85C DC And AC Voltage Derating Is 1.25%/C. |

### Dimensions

|    |                   |
|----|-------------------|
| L  | 10mm +0.2mm       |
| H  | 8mm +0.1mm        |
| T  | 3mm +0.1mm        |
| S  | 7.5mm +0.6/-0.1mm |
| H0 | 18.5mm +/-0.5mm   |
| F  | 0.5mm +/-0.05mm   |

### Packaging Specifications

|                    |                         |
|--------------------|-------------------------|
| Packaging          | Ammo, 360x340x59mm, Box |
| Packaging Quantity | 2800                    |

### Specifications

|                       |                     |
|-----------------------|---------------------|
| Capacitance           | 0.47 uF             |
| Tolerance             | 5%                  |
| Voltage DC            | 63 VDC              |
| Voltage AC            | 40 VAC              |
| Temperature Range     | -55/+105°C          |
| Rated Temperature     | 85°C                |
| Dissipation Factor    | 1% 1kHz, 1.5% 10kHz |
| Insulation Resistance | 2.6596 GOhms        |
| Max dV/dt             | 120 V/us            |
| Inductance            | 8 nH                |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.