

## R75QI215050H0J

Aliases (75QI215050H0J)

R75H, Film, Metallized Polypropylene, Automotive Grade, 0.015 uF, 5%, 1,000 VDC, 105°C, 15 mm



Click [here](#) for the 3D model.

### General Information

Series	R75H
Dielectric	Metallized Polypropylene
Style	Radial
Features	Automotive Grade, Pulse
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
Qualifications	AEC-Q200
Typical Component Weight	1.4 g
Miscellaneous	Above 105C DC And AC Voltage Derating Is 1.25%/C.

### Dimensions

L	18mm +0.3/-0.5mm
H	11mm +0.1/-0.5mm
T	5mm +0.2/-0.5mm
S	15mm +/-0.4mm
LL	25mm +2/-1mm
F	0.8mm +/-0.05mm

### Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	1000

### Specifications

Capacitance	0.015 uF
Tolerance	5%
Voltage DC	1000 VDC
Voltage AC	250 VAC
Temperature Range	-55/+125°C
Rated Temperature	105°C
Dissipation Factor	0.04% 1kHz, 0.06% 10kHz, 0.25% 100kHz
Insulation Resistance	100 GOhms
Max dV/dt	2,000 V/us
ESR	74.3 mOhms (100kHz)
Ripple Current	2.11 Amps (100kHz 90C), 30 Amps (Peak)
Inductance	10 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.