


R76MD1390SE30J

Aliases (76MD1390SE30J)

R76, Film, Double Metallized Polypropylene, Automotive Grade, 3,900 pF, 5%, 400 VDC, 85°C, 7.5 mm



Click [here](#) for the 3D model.

General Information

| | |
|--------------------------|---------------------------------|
| Series | R76 |
| Dielectric | Double Metallized Polypropylene |
| Style | Radial |
| Features | Automotive Grade, Pulse |
| RoHS | Yes |
| Termination | Cut (Tinned Wire) |
| Lead | Cut |
| Qualifications | AEC-Q200 |
| Typical Component Weight | 0.34 g |

Dimensions

| | |
|----|------------------|
| L | 10mm +0.2/-0.5mm |
| H | 8mm +0.1/-0.5mm |
| T | 3mm +0.1/-0.5mm |
| S | 7.5mm +/-0.4mm |
| LL | 4mm +2mm |
| F | 0.5mm +/-0.05mm |

Packaging Specifications

| | |
|--------------------|------|
| Packaging | Bulk |
| Packaging Quantity | 1500 |

Specifications

| | |
|-----------------------|--------------------------------------|
| Capacitance | 3,900 pF |
| Tolerance | 5% |
| Voltage DC | 400 VDC |
| Voltage AC | 250 VAC |
| Temperature Range | -55/+110°C |
| Rated Temperature | 85°C |
| Dissipation Factor | 0.03% 1kHz, 0.04% 10kHz, 0.1% 100kHz |
| Insulation Resistance | 100 GOhms |
| Max dV/dt | 1,700 V/us |
| ESR | 163.24 mOhms (100kHz) |
| Ripple Current | 0.6 Amps (100kHz 85C), 7 Amps (Peak) |
| Inductance | 8 nH |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.