
SCEQP5006Y2R7SC000

SCE, Supercapacitors, Snap-In, 500 F, 30%, 2.7 VDC, 2 Pin, 26.6 mm



General Information	
Series	SCE
Style	Snap-In
Description	Radial Cylindrical Double Layer Capacitor
RoHS	Yes
Lead	2 Pin
AEC-Q200	No
Construction	Organic Electrolyte

Click here for the 3D model.

Dimensions	
D	35mm +/-1.5mm
L	70mm +/-2mm
S	26.6mm +/-0.1mm
LL	3.5mm +/-0.5mm

Packaging Specifications	
Packaging	Carton Box

Specifications	
Capacitance	500 F
Tolerance	30%
Voltage DC	2.7 VDC
Temperature Range	-40/+70°C
ESR	1.2 mOhms (1kHz), 1.6 mOhms (Max DC IEC)
Leakage Current	1.4 mA (72 Hrs)
Maximum Continuous Current	28.48 A

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

© 2006 - 2026 YAGEO