



Click [here](#) for the 3D model.

General Information

Series	SCV
Style	Radial
Description	Radial Cylindrical Double Layer Capacitor
RoHS	Yes
Lead	Wire Leads
Construction	Organic Electrolyte
Typical Component Weight	1.58 g

Dimensions

D	8mm +/-1mm
L	20mm +/-2mm
S	3.5mm +/-0.5mm
F	0.6mm +/-0.05mm

Packaging Specifications

Packaging	Carton Box
Packaging Quantity	3000

Specifications

Capacitance	3.3 F
Tolerance	30%
Voltage DC	3 VDC
Temperature Range	-40/+65°C
ESR	100 mOhms (1kHz), 150 mOhms (Max DC IEC)
Leakage Current	0.014 mA (72 Hrs)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.