



Click [here](#) for the 3D model.

General Information

Series	SCT
Style	Radial
Description	Radial Cylindrical Double Layer Capacitor
RoHS	Yes
Lead	Wire Leads
Construction	Organic Electrolyte
Typical Component Weight	1.29 g

Dimensions

D	8mm +/-1mm
L	16mm +/-2mm
S	3.5mm +/-0.5mm
LL Negative	15mm MIN
LL Positive	19mm MIN
F	0.6mm +/-0.05mm

Packaging Specifications

Packaging	Carton Box
Packaging Quantity	3500

Specifications

Capacitance	2 F
Tolerance	30%
Voltage DC	2.7 VDC
Temperature Range	-40/+85°C
Rated Temperature	85°C
ESR	120 mOhms (1kHz), 180 mOhms (Max DC IEC)
Leakage Current	0.01 uA (72 Hrs)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.