



Click [here](#) for the 3D model.

General Information

Series	SCT
Style	Snap-In
Description	Radial Cylindrical Double Layer Capacitor
Features	Automotive
RoHS	Yes
Lead	Wire Leads
Qualifications	AEC-Q200
Construction	Organic Electrolyte

Dimensions

D	8mm +/-1mm
L	20mm +/-2mm
S	3.5mm +/-0.5mm
F	0.6mm +/-0.05mm

Packaging Specifications

Packaging	Carton Box
-----------	------------

Specifications

Capacitance	3.3 F
Tolerance	-20/+50%
Voltage DC	2.7 VDC
Temperature Range	-40/+85°C
ESR	100 mOhms (1kHz), 150 mOhms (Max DC IEC)
Leakage Current	0.012 mA (72 Hrs)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.