

T398G106K035AS

T398, Tantalum, MnO₂ Tantalum, Commercial Grade, 10 uF, 10%, 35 VDC, Radial, Solid Tantalum, Three Leaded



Click [here](#) for the 3D model.

General Information

Series	T398
Dielectric	MnO ₂ Tantalum
Style	Radial Three Lead
Description	Radial, Solid Tantalum, Three Leaded
RoHS	No
Prop 65	WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov/
SCIP Number	78c25989-fc86-4b0d-a598-1bcecbae95c0
Termination	Lead (SnPb)
Construction	Conformal

Specifications

Capacitance	10 uF
Tolerance	10%
Voltage DC	35 VDC (85C), 23 VDC (125C), 0.35 VDC (125C Reverse)
Temperature Range	-55/+125°C
Dissipation Factor	6%
Leakage Current	2.8 uA

Dimensions

W	7.1mm
H	11.2mm
T	6.3mm
S	2.54mm +/-0.2mm
LL	4.75mm +/-1.27mm
F	0.5mm +/-0.05mm

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	500

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.