

T540D337M2R5DH8605

T540 HRA, Tantalum, Polymer Tantalum, HRA, 330 uF, 20%, 2.5 VDC, SMD, Polymer, Molded, High Reliability, D (0.001%/1000 Hrs), 40 mOhms, 3.1 mm, 2817 / 7343



Click [here](#) for the 3D model.

General Information

| | |
|--------------------------|--|
| Series | T540 HRA |
| Dielectric | Polymer Tantalum |
| Style | SMD Chip |
| Description | SMD, Polymer, Molded, High Reliability |
| Features | Non-Combustible, Low ESR, High Reliability |
| RoHS | No |
| Prop 65 | WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov/ |
| SCIP Number | b064b03e-bd75-42af-b342-1fe94dec2340 |
| Termination | Tin Lead (SnPb) |
| Typical Component Weight | 352.36 mg |
| Shelf Life | 52 Weeks |
| MSL | 3 |

Dimensions

| | |
|---|--------------------|
| L | 7.3mm +/-0.3mm |
| W | 4.3mm +/-0.3mm |
| H | 2.8mm +/-0.3mm |
| T | 0.13mm REF |
| S | 1.3mm +/-0.3mm |
| F | 2.4mm +/-0.1mm |
| A | 3.8mm MIN |
| B | 0.5mm +/-0.15mm |
| E | 3.5mm REF |
| G | 3.5mm REF |
| P | 0.9mm REF |
| R | 1mm REF |
| X | 0.1mm +/-0.1mm REF |

Packaging Specifications

| | |
|--------------------|------------|
| Packaging | T&R, 178mm |
| Packaging Quantity | 500 |

Specifications

| | |
|-------------------------|---|
| Capacitance | 330 uF |
| Tolerance | 20% |
| Voltage DC | 2.5 VDC (105C), 1.68 VDC (125C) |
| Temperature Range | -55/+125°C |
| Rated Temperature | 105°C |
| Life | 2000 Hrs (125C) |
| Humidity | 85C, 85% RH, 1000 Hours, rated voltage |
| Dissipation Factor | 10% 120Hz 25C |
| Failure Rate | D (0.001%/1000 Hrs) |
| ESR | 40 mOhms (100kHz 25C) |
| Ripple Current | 2372 mA (rms, 100kHz 45C) |
| Leakage Current | 83 uA (5min 25°C) |
| Testing and Reliability | 10 Cycles At 25C +/-5C & Improved Humidity Capability |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.